

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010195](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Turned Crimp Contact for 16A Male S-EHV Inserts, Silver (Ag) Plated Copper Alloy, 1.50mm² (16 AWG), 100 per Bag

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191876030

Physical

Gender	Male
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	1.300/g
Number of Grooves	2
Packaging Type	Bag
Stripping Length	7.50mm

Electrical

Current - Maximum per Contact	16.0A
-------------------------------	-------

Material Info

Engineering Number	7300.6257.0
--------------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)
lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Female Turned Crimp Contact

Use With

Male S-EHV Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0195](#)