

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010443](#)
Status: **Active**
Overview:
Description: GWconnect Crimp Terminal Insert, Female, 7-Pole, 10A, Size 3A «21x21»

Agency Certification

UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 3A «21x21»
 Component Type Inserts - Crimp Contact
 Insert Series S-Q7/0
 Overview hdc_heavy_duty_connectors
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
 UPC 887191891019

Physical

Durability (mating cycles max) 500
 Flammability UL 94V-0
 Gender Female
 Insert Color Grey
 Material - Insert Polycarbonate
 Net Weight 13.500/g
 Number of Rows 3
 Packaging Type Bag
 Polarized to Mating Part Yes
 Poles 7
 Stripping Length 7.50mm
 Temperature Range - Operating -40° to +125°C
 Tightening Test Torque 0.25 Nm

Electrical

Current - Maximum per Contact 10.0A
 Voltage - Maximum 400V

Material Info

Engineering Number 7607.5802.0

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 ED/71/2019 (16 July
 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601](#) Series

Mates With

[936010444](#) Male Screw Axial Terminal
 Insert

Use With

Size 3A «21x21» Hoods and Housings

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0443](#)