

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010444](#)  
**Status:** **Active**  
**Overview:**  
**Description:** GWconnect Crimp Terminal Insert, Male, 7-Pole, 10A, Size 3A «21x21»

**Agency Certification**

UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
 Series [93601](#)  
 Component Size 3A «21x21»  
 Component Type Inserts - Crimp Contact  
 Insert Series S-Q7/0  
 Overview hdc\_heavy\_duty\_connectors  
 Product Category Heavy Duty Connectors  
 Product Name GWconnect  
 Standard CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977  
 UPC 887191891026

**Physical**

Durability (mating cycles max) 500  
 Flammability UL 94V-0  
 Gender Male  
 Insert Color Grey  
 Material - Insert Polycarbonate  
 Net Weight 13.500/g  
 Number of Rows 3  
 Packaging Type Bag  
 Polarized to Mating Part Yes  
 Poles 7  
 Stripping Length 7.50mm  
 Temperature Range - Operating -40° to +125°C  
 Tightening Test Torque 0.25 Nm

**Electrical**

Current - Maximum per Contact 10.0A  
 Voltage - Maximum 400V

**Material Info**

Engineering Number 7607.5902.0

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per - ED/71/2019 (16 July 2019)

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[93601](#) Series

**Mates With**

[936010443](#) Female Screw Axial Terminal Insert

**Use With**

Size 3A «21x21» Hoods and Housings

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0444](#)