

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010462](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect Turned Crimp Contact for 100A Inserts and Modules, Female, Silver (Ag) Plated Copper Alloy, 10.00mm² (7 AWG), 100 per Bag

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Contact Type	Turned Crimp
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Contacts
Product Name	GWconnect
UPC	887191891705

Physical

Gender	Female
Material - Contact	Copper Alloy
Material - Plating	Silver
Net Weight	12.200/g
Number of Grooves	0
Packaging Type	Bag
Stripping Length	19.00mm
Wire Size AWG	7
Wire Size mm ²	10.00

Electrical

Current - Maximum per Contact	100.0A
-------------------------------	--------

Material Info

Engineering Number	7700.3131.0
--------------------	-------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[93601](#) Male Turned Crimp Contact

Use With

S-K and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0462](#)