

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010500](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** Gwconnect Shielded S-CX/75 Series 75 Ohm Coaxial Connector, Male, 1-Pole

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Comments	Contact to be ordered Separately.
Component Type	Coaxial Connector
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191824192

**Physical**

Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Material - Insert	Polycarbonate
Material - Shield/Shell	Zinc Alloy-Nickel Plated
Net Weight	21.800/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	1
Temperature Range - Operating	-40° to +85°C
Wire Size AWG	26-14
Wire Size mm <sup>2</sup>	0.14-2.50

**Electrical**

Current - Maximum per Contact	10.0A
Voltage	EN 61984: 50V 0.8kV 3

**Material Info**

Engineering Number	7701.3510.0
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Mates With**

[936010499](#) Female 75 Ohm Coaxial Connector

**Use With**

S-D Series Coaxial 10.0A Male Turned Crimp Contact

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0500](#)