

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010546](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: Gwconnect S-CX/8 Shielded Circular BUS Connector, Male, 8-Pole

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Contacts to be ordered Separately.
Component Type	Circular BUS Connector
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191832661

Physical

Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Material - Insert	Polycarbonate
Material - Shield/Shell	Zinc Alloy-Nickel Plated
Net Weight	28.700/g
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	8
Temperature Range - Operating	-40° to +85°C
Wire Size AWG	28-20
Wire Size mm ²	0.08-0.50

Electrical

Current - Maximum per Contact	5.0A
Voltage	EN 61984: 50V 0.8kV 3

Material Info

Engineering Number	7708.3520.0
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601](#) Series

Mates With

[936010545](#) Female Circular BUS Connector

Use With

D-Sub 5.0A Male Turned Crimp Contact

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0546](#)