

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936010574](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** GWconnect HP-HE - High Performance-Harsh Environment, Screw Locking Hood, Zinc Alloy, Top Entry, Size 3A «21x21», M20 Thread, Black

**Documents:**  
[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93601</a>
Component Size	3A «21x21»
Component Type	Screw Locking Hood
Number of Screws	2
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191835815

**Physical**

Entry Location	Top
Hood Coating	Epoxy-Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Zinc Alloy
Net Weight	74.800/g
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric

**Material Info**

Engineering Number	7803.3443.3
--------------------	-------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93601 Series](#)

**Use With**

Size 3A «21x21» S-A 3/4, S-D7, S-Q 2/0, S-Q 5/0 Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-0574](#)