

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011007](#)

Status: **Active**

Overview:

Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 1 Lever, Right Side Entry, Size 6B «44x27», Extended M20 Thread, Grey

Agency Certification

| | |
|-----|---------|
| CSA | 256883 |
| UL | E249674 |

General

| | |
|------------------|---|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93601 |
| Component Size | 6B «44x27» |
| Component Type | Single Lever Hood |
| IP Rating | IP66 |
| Overview | hdc_heavy_duty_connectors |
| Product Category | Heavy Duty Connectors |
| Product Name | GWconnect |
| Type | STD |
| UPC | 887191865140 |

Physical

| | |
|------------------|-------------------|
| Entry Location | Side |
| Material - Hood | Die-cast Aluminum |
| Material - Lever | Galvanized Steel |
| Net Weight | 134.300/g |
| Number of Levers | 1 |
| Packaging Type | Bag |
| Thread Size | M20 |
| Thread Type | (M) Metric |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 7806.7450.0 |
|--------------------|-------------|

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

| | |
|-----------------|--------------|
| China ROHS | Not Reviewed |
| ELV | Not Reviewed |
| RoHS Phthalates | Not Reviewed |

China RoHS

Search Parts in this Series

[93601](#) Series

Use With

Size 6B <<44x27>> S-DD, S-E, S-EE, S-EP, S-ES, and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1007](#)