

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011103](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HP-HE - High Performance-Harsh Environment, Toggle Locking Hood, Zinc Alloy, Size 10B «57x27», Pg29 Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Toggle Locking Hood
IP Rating	IP68, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191871103

Physical

Entry Location	Side
Hood Coating	Epoxy-Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Zinc Alloy
Packaging Type	Bag
Thread Size	Pg29
Thread Type	(Pg)

Material Info

Engineering Number	7810.3842.8
--------------------	-------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size 10B «57x27» S-D, S-DD, S-E, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1103](#)