

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936011322](#)

**Status:** **Active**

**Overview:** [GWconnect® Heavy Duty Connectors \(HDC\)](#)

**Description:** GWconnect HE-HV - Harsh Environment-High Voltage, Double Lever Hood, Die-cast Aluminum, with 2 Levers, Top Entry, Size 10B «57x27», Pg21 Thread, High Construction, Black

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA 256883  
UL E249674

**General**

Product Family Industrial Connectors / Enclosures  
Series [93601](#)  
Component Size 10B «57X27»  
Component Type Double Lever Hood  
IP Rating IP66, IP69  
Overview [GWconnect® Heavy Duty Connectors \(HDC\)](#)  
Product Category Heavy Duty Connectors  
Product Name GWconnect  
Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984  
Type HE-HV  
UPC 887191884295

**Physical**


Entry Location Top  
Hood Coating Polyester Powder  
Hood Color Black RAL 9005  
Lock to Mating Part Yes  
Material - Hood Die-cast Aluminum  
Material - Lever Galvanized Steel  
Number of Levers 2  
Packaging Type Bag  
Thread Size Pg21  
Thread Type (Pg)

**Electrical**

Voltage - Maximum 830V

**Material Info**

Engineering Number 7810.5072.8



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

**Search Parts in this Series**

[93601](#) Series

**Use With**

Size 10B «57x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-1322](#)