

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012004](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect HE-HV - Harsh Environment-High Voltage, Double Lever Surface Mount Housing, Die-cast Aluminum, with 2 Levers, without Gasket, Size 10B «57x27», Pg21 Thread, Black, High Construction

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 10B «57X27»
 Component Type Double Lever SMT Housing
 IP Rating IP66, IP69
 Overview [GWconnect® Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type HE-HV
 UPC 887191863894

Physical

Housing Coating Polyester Powder
 Housing Color Black RAL 9005
 Lock to Mating Part Yes
 Material - Housing Die-cast Aluminum
 Material - Lever Galvanized Steel
 Mounting Style Surface Mount
 Net Weight 360.930/g
 Number of Levers 2
 Packaging Type Bag
 Thread Size Pg21
 Thread Type (Pg)

Electrical

Voltage - Maximum 830V

Material Info

Engineering Number 7810.7464.3



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 10B «57x27» , S-EHV Inserts with Screw Terminals and S-HSB Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2004](#)