

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012020](#)

Status: **Active**

Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)

Description: GWconnect EMC - Electromagnetic Compatibility, Double Lever Surface Mount Housing, Aluminum, with 2 Levers, with Gasket, Size 10B «57x27», Pg29x2 Thread, High Construction

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	10B «57X27»
Component Type	Double Lever SMT Housing
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191865256

Physical

Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Aluminum
Material - Lever	Galvanized Steel
Mounting Style	Surface Mount
Number of Levers	2
Packaging Type	Bag
Thread Size	Pg29x2
Thread Type	(Pg)

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number	7810.7467.4
--------------------	-------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size 10B «57x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-HSB, S-K and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2020](#)