

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012079](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HP-HE - High Performance-Harsh Environment, Surface Mount Housing, Screw Locking, Zinc Alloy, Side Entry, Size 16B «77x27», M25 Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	Screw Locking
Component Size	16B «77X27»
Component Type	Surface Mount Housing
IP Rating	IP68, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191869346

Physical

Housing Coating	Epoxy-Polyester Powder
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Housing	Zinc Alloy
Mounting Style	Surface Mount
Net Weight	1011.000/g
Packaging Type	Bag
Thread Size	M25
Thread Type	(M) Metric

Material Info

Engineering Number	7816.3780.3
--------------------	-------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2079](#)