

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012128](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Surface Mount Housing, Die-cast Aluminum, with 1 Lever, Size 16A «66x16», M25x2 Thread, Grey

Documents:

3D Model	3D Model (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16A «66X16»
Component Type	Single Lever SMT Housing
IP Rating	IP66
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191872339

Physical

Housing Coating	Polyester Powder
Housing Color	Grey RAL 7037
Lock to Mating Part	Yes
Material - Housing	Die-cast Aluminum
Material - Lever	Stainless Steel
Mounting Style	Surface Mount
Net Weight	197.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M25x2
Thread Type	(M) Metric

Electrical


Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number	7816.4524.0
--------------------	-------------

Reference - Drawing Numbers

Sales Drawing	936012121-000
---------------	---------------



EU ELV

Not Relevant

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size 16A «66x16» S-A and S-D Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2128](#)