

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012172](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect HE - Harsh Environment, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Side Entry, Size 16A «66x16», Pg16 Extended Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Component Size 16A «66X16»
 Component Type Single Lever Hood
 IP Rating IP66, IP69
 Overview [GWconnect® Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type HE
 UPC 887191874777

Physical

Entry Location Top
 Hood Coating Polyester Powder
 Hood Color Black RAL 9005
 Lock to Mating Part Yes
 Material - Hood Die-cast Aluminum
 Material - Peg Stainless Steel
 Number of Pegs 2
 Packaging Type Bag
 Thread Size Pg16
 Thread Type (Pg)

Electrical

Voltage - Maximum 500V

Material Info

Engineering Number 7816.4558.1



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
 Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 16A 66x16» S-A and S-D Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2172](#)