

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936012586](#)
Status: **Active**
Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect EMC - Electromagnetic Compatibility, Double Lever Hood, Aluminum, with 4 Pegs, Top Entry, Size 16B «77x27», without Gasket, Pg21 Extended Threaded Fitting, High Construction

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	16B «77X27»
Component Type	Double Lever Hood
IP Rating	IP66, IP69
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	EMC
UPC	887191835723

Physical

Entry Location	Top
Lock to Mating Part	Yes
Material - Hood	Aluminum
Material - Peg	Stainless Steel
Net Weight	261.500/g
Number of Pegs	4
Packaging Type	Bag
Thread Size	Pg21
Thread Type	(Pg)

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number	7816.6423.4
--------------------	-------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 16B «77x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-HSB, S-K and S-M Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-2586](#)