

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013110](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect HP-HE - High Performance-Harsh Environment, Screw Locking Hood, Zinc Alloy, Top Entry, Size 24B «104x27», M40x2 Thread, Black

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Screw Locking Hood
IP Rating	IP68, IP69
Material - Screw	Stainless Steel
Number of Screws	2
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	HP-HE
UPC	887191871240

Physical

Entry Location	Top
Hood Coating	Epoxy-Polyester Powder
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Hood	Zinc Alloy
Net Weight	691.000/g
Packaging Type	Bag
Thread Size	M40x2
Thread Type	(M) Metric

Material Info

Engineering Number	7824.3681.8
--------------------	-------------



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[93601 Series](#)

Use With

Size 24B «104x27» S-D, S-DD, S-E, S-ES, S-EP, S-EE, S-EEE, S-HSB, S-K, and S-M Inserts

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3110](#)