

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936013485](#)

Status: **Active**

Overview: [GWconnect® Heavy Duty Connectors \(HDC\)](#)

Description: GWconnect STD - Standard, Double Lever Hood, Die-cast Aluminum, with 4 Pegs, Top Entry, Size 24B «104x27», Black, with IP66 - Ribbon Cable Gland, Grey, Cable Size 4.50-5.70mm x 72.00-76.00mm, High Construction

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA	256883
UL	E249674

General

Product Family	Industrial Connectors / Enclosures
Series	93601
Cable Gland Type	IP66 - Ribbon Cable
Component Size	24B «104X27»
Component Type	Double Lever Hood
Overview	GWconnect® Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191839998

Physical

Entry Location	Top
Flammability	UL 94V-0
Gland Color	Grey RAL 7037
Hood Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Cable Gland	Polyamide
Material - Gasket	Silicone
Material - Hood	Die-cast Aluminum
Material - Peg	Stainless Steel
Number of Pegs	4
Packaging Type	Bag
Ribbon Cable Size	4.50-5.70mm X 72.00-76.00mm
Temperature Range - Operating	-40°C to +100°C
Waterproof / Dustproof	Yes
Waterproof / Dustproof Type	IP66, IP69

Electrical

Voltage - Maximum	500V
-------------------	------

Material Info

Engineering Number	7824.5375.1
--------------------	-------------



Series image - Reference only

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	Not Reviewed
ELV	Not Reviewed
RoHS Phthalates	Not Reviewed

Search Parts in this Series

[93601](#) Series

Use With

Size 24B «104x27» S-D, S-DD, S-E, S-EE, S-EP, S-ES, S-HSB, S-ESHV, S-K,S-M, and S-EHV Inserts and Ribbon Cable

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93601-3485](#)