

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936030014](#)

Status: **Active**

Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)

Description: GWconnect Connector Kit, 3 Pole, Series S-A Female-Male Inserts, M20 Metal Cable Gland, M20 Die-cast Aluminum Hood-Top Entry, Bulkhead Housing-Right Angle, 1 Lever, Size 3A «21x21», Grey

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

Kit components

Kit Components [936000046](#) M20 Gland, [936010682](#) M20 Hood, [936010125](#) Male Insert, [936010121](#) Female Insert, [936010622](#) Right Angle Bulkhead Housing

General

Product Family Industrial Connectors / Enclosures
Series [93603](#)
Color - Cable Jacket N/A
Component Size 3A «21x21»
Component Type Connector Kit - Female+Male
Insert Series S-A
Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
Product Category Heavy Duty Connectors
Product Name GWconnect
UPC 887191860220

Physical

Lock to Mating Part Yes
Mounting Style Bulkhead
Net Weight 165.000/g
Packaging Type Bag
Thread Size M20
Thread Type (M) Metric

Electrical

Current - Maximum per Contact 10.0A
Voltage - Maximum 230V / 400V

Material Info

Engineering Number 7903.7745.5



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - ED/71/2019 (16 July 2019)

Lead

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

50 Image

Not Relevant

Not Contained

Search Parts in this Series

[93603](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93603-0014](#)