

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936030059](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Connector Kit, 10 Pole, Series S-E Female-Male Inserts, M20 Die-cast Aluminum Hood-Side Entry-Top Entry, Bulkhead Mount Housing-Vertical, 2 Lever, Size 10B «57x27», Grey](#)

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Kit components

Kit Components [936011746](#) M20 Hood, [936010238](#) Male Insert, [936010231](#) Female Insert, [936011559](#) Vertical Bulkhead Housing

General

Product Family Industrial Connectors / Enclosures
 Series [93603](#)
 Component Size 10B «57X27»
 Component Type Connector Kit - Female+Male
 Insert Series S-E
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 UPC 887191863436

Physical


Lock to Mating Part Yes
 Mounting Style Bulkhead
 Net Weight 400.000/g
 Packaging Type Bag
 Thread Size M20
 Thread Type (M) Metric

Electrical

Current - Maximum per Contact 16.0A
 Voltage - Maximum 500V

Material Info

Engineering Number 7910.7755.0



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93603](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93603-0059](#)