

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936040190](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: [GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 58 x 64 x 36mm Outside Dimensions, Sandblasted](#)

Documents:

[RoHS Certificate of Compliance \(PDF\)](#)

General


Product Family	Industrial Connectors / Enclosures
Series	93604
IP Rating	IP66, IP69
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2
Type	Sandblasted
UPC	887191878652

Physical

Internal Dimensions	51 x 57 x 30mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	Internal Through Holes
Net Weight	220.000/g
Outside Dimensions	58 x 64 x 36mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C

Material Info

Engineering Number	8100.8206.0
--------------------	-------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93604 Series](#)

Use With

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93604-0190](#)