

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0936040252](#)  
**Status:** **Active**  
**Overview:** [GWconnect Heavy Duty Connectors \(HDC\)](#)  
**Description:** [GWconnect Enclosure, Die-cast Aluminum, S-8100 Series, without External Mounting Flanges, 150 x 64 x 36mm Outside Dimensions, Black RAL 9005](#)

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Connectors / Enclosures
Series	<a href="#">93604</a>
IP Rating	IP66, IP69
Overview	<a href="#">GWconnect Heavy Duty Connectors (HDC)</a>
Product Category	Die-cast Enclosures
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 62208, NEMA ICS5, NEMA250, NMX-J235/1-2
Type	STD
UPC	887191882277

**Physical**

Enclosure Coating	Polyester Powder
Enclosure Color	Black RAL 9005
Internal Dimensions	143 x 57 x 29mm
Material - Enclosure	Die-cast Aluminum
Mounting Style	Internal Through Holes
Net Weight	319.000/g
Outside Dimensions	150 x 64 x 36mm
Packaging Type	Carton
Temperature Range - Operating	-40° to +125°C

**Material Info**

Engineering Number	8100.8308.1
--------------------	-------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Relevant

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[93604 Series](#)

**Use With**

DIN-rails, mounting supports, fixing screws, metal plates, and ground terminals

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[93604-0252](#)