

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0945180100](#)
Status: **Active**
Description: High Normal Force Tabs, Unplated Brass, AWG 18-20

Documents:

[Drawing \(PDF\)](#) [Test Summary TS-94518-001-001 \(PDF\)](#)
[Packaging Specification 945180001-PK-000 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family Crimp Terminals
Series [94518](#)
Application Power, Wire-to-Board
Crimp Quality Equipment Yes
Product Name High Normal Force (HNF) Termin
UPC 800754333313

Physical

Gender Female
Material - Metal Brass
Material - Plating Mating Unplated
Material - Plating Termination Unplated
Net Weight 0.670/g
Packaging Type Reel
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 2.20-2.80mm
Wire Size AWG 18, 20
Wire Size mm² 0.50-1.00


Solder Process Data

Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers

Packaging Specification 945180001-PK-000
Sales Drawing 945180001-000, SD-94518-005-001
Test Summary TS-94518-001-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

[94518 Series](#)

Application Tooling | [FAQ](#)

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extraction and Activation Tool	638132700
Hand Tool for RAST5 Normal Force Female Crimp Terminals	638253500
FineAdjust Applicator for RAST5 Normal Force Female Crimp Terminal	639019700

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[94518-0100](#)