

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0982660234](#)  
**Status:** **Active**  
**Overview:** FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers  
**Description:** 0.50mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 102.00mm Cable Length, Tin (Sn) Plating, 22 Circuits

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PS-98266-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Packaging Specification PK-98266-001-001 (PDF)</a>	

**General**

Product Family	Cable
Series	98266
Comments	Contacts on opposite sides, Type D
Crimp Quality Equipment	Yes
Overview	<a href="#">FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers</a>
Product Name	Premo-Flex FFC Jumper
UPC	756054771815

**Physical**

Cable Length	102.00mm
Circuits (Loaded)	22
Contact Layout Type	D (opposite side)
Material - Plating Mating	Tin
Net Weight	0.742/g
Packaging Type	Bag
Pitch - Mating Interface	0.50mm
Temperature Range - Operating	-40° to +105°C
Wire Size AWG	N/A
Wire/Cable Type	Flat Flex Cable

**Electrical**

Current - Maximum per Contact	0.5A
Voltage - Maximum	60V AC

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-98266-001-001
Product Specification	PS-98266-001-001
Sales Drawing	SD-98266-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[98266 Series](#)

**Mates With**

Easy-On FFC/FPC Connector: <br>  
[524352233](#) , [524372233](#) , [5019512200](#) ,  
[525592234](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98266-0234](#)