

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982670782](#)
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.00mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 229.00mm Cable Length, Tin (Sn) Plating, 9 Circuits

Documents:

| | |
|--|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification PS-98267-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 98267 |
| Comments | Contacts on opposite sides, Type D |
| Crimp Quality Equipment | Yes |
| Overview | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 800756948041 |

Physical

| | |
|-------------------------------|-------------------|
| Cable Length | 229.00mm |
| Circuits (Loaded) | 9 |
| Contact Layout Type | D (opposite side) |
| Material - Plating Mating | Tin |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.00mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.2A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------|
| Product Specification | PS-98267-001-001 |
| Sales Drawing | SD-98267-001-001 |



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[98267 Series](#)

Mates With

Easy-On FFC/FPC Connector:

[522070933](#) , [522710979](#) , [526100933](#) ,
[526100934](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98267-0782](#)