

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0982680362](#)
Status: **Active**
Overview: FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers
Description: 1.25mm Pitch Premo-Flex FFC Jumper, Opposite Side Contacts (Type D), 254.00mm Cable Length, Tin (Sn) Plating, 28 Circuits

Documents:

| | |
|--|--|
| Drawing (PDF) | Datasheet (PDF) |
| Product Specification PS-98268-001-001 (PDF) | RoHS Certificate of Compliance (PDF) |

General

| | |
|-------------------------|---|
| Product Family | Cable |
| Series | 98268 |
| Comments | Contacts on opposite sides, Type D |
| Crimp Quality Equipment | Yes |
| Overview | FFC Cable Jumpers, Premo-Flex Flat-Flexible Cable Jumpers |
| Product Name | Premo-Flex FFC Jumper |
| UPC | 756054778708 |

Physical

| | |
|-------------------------------|-------------------|
| Cable Length | 254.00mm |
| Circuits (Loaded) | 28 |
| Contact Layout Type | D (opposite side) |
| Material - Plating Mating | Tin |
| Net Weight | 6.047/g |
| Packaging Type | Bag |
| Pitch - Mating Interface | 1.25mm |
| Temperature Range - Operating | -40° to +105°C |
| Wire Size AWG | N/A |
| Wire/Cable Type | Flat Flex Cable |

Electrical

| | |
|-------------------------------|--------|
| Current - Maximum per Contact | 1.4A |
| Voltage - Maximum | 60V AC |

Material Info

Reference - Drawing Numbers

| | |
|-----------------------|------------------|
| Product Specification | PS-98268-001-001 |
| Sales Drawing | SD-98268-001-001 |



EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[98268 Series](#)

Mates With

Molex FFC – FPC connector. Be sure to match like plating.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[98268-0362](#)