

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1002973401](#)
Status: **Active**
Overview: [zQSFP+® Interconnect System](#)
Description: [zQSFP+-to-zQSFP+ Cable Assembly, 26 AWG, 4.0m Length](#)

Documents:

Drawing (PDF)	Test Summary 1002970020-000 (PDF)
Test Summary 1002970003-000 (PDF)	Test Summary 1002970021-000 (PDF)
Test Summary 1002970004-000 (PDF)	Test Summary 1002970023-000 (PDF)
Test Summary 1002970006-000 (PDF)	Test Summary TS-100297-3401-001 (PDF)
Test Summary 1002970007-000 (PDF)	RoHS Certificate of Compliance (PDF)
Test Summary 1002970008-000 (PDF)	Product Literature (PDF)
Test Summary 1002970009-000 (PDF)	



General

Product Family	Cable Assemblies
Series	100297
Assembly Configuration	Dual Ended Connectors
Connector to Connector	QSFP28-to-QSFP28, zQSFP+-to-zQSFP+
Overview	zQSFP+® Interconnect System
Product Name	zQSFP Plus, zQSFP+
UPC	887191650104

Physical

Cable Length	4.0m
Circuits (Loaded)	38
Gender	Plug/Plug
Lock to Mating Part	Yes
Material - Metal	Zinc Die Cast
Net Weight	1.000/g
Number of Rows	2
Packaging Type	Bag
Single Ended	No
Wire Size AWG	26
Wire/Cable Type	Round

Electrical

Current - Maximum per Contact	0.03A
Impedance	100Ω
Shielded	No
Voltage - Maximum	3.3V DC

Material Info

Reference - Drawing Numbers

Sales Drawing	1002970001-000
Test Summary	1002970003-000, 1002970004-000, 1002970006-000, 1002970007-000, 1002970008-000, 1002970009-000, 1002970020-000, 1002970021-000, 1002970023-000, TS-100297-3401-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

100297 Series

Mates With

zQSFP Cages and Connectors

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[100297-3401](#)