

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1053102310](#)  
**Status:** **Active**  
**Overview:** [Nano-Fit Power Connectors](#)  
**Description:** Nano-Fit Vertical Header, Through Hole, 2.50mm Pitch, Dual Row, 10 Circuits, with Kinked Pins, 0.76µm Gold (Au) Plating, Natural, Glow-Wire Capable, Tray

**Documents:**

|  |   |
|--|---|
| <a href="#">Drawing (PDF)</a>                                    | <a href="#">Product Specification PS-105300-100-001 (PDF)</a>     |
| <a href="#">3D Model (PDF)</a>                                   | <a href="#">Application Specification AS-105300-100-001 (PDF)</a> |
| <a href="#">3D Model</a>   | <a href="#">Packaging Specification PK-105309-100-000 (PDF)</a>   |
| <a href="#">Product Specification 1053001000-PS-CH-000 (PDF)</a> | <a href="#">Test Summary 1053000000-TS-000 (PDF)</a>              |
| <a href="#">Product Specification 1053001000-PS-ES-000 (PDF)</a> | <a href="#">Datasheet (PDF)</a>                                   |
| <a href="#">Product Specification 1053001000-PS-JP-000 (PDF)</a> | <a href="#">Symbol Footprint Data SYM-105310-XX10-001 (PDF)</a>   |
| <a href="#">Product Specification 1053001000-PS-SK-000 (PDF)</a> | <a href="#">RoHS Certificate of Compliance (PDF)</a>              |

**Agency Certification**


|     |         |
|-----|---------|
| CSA | LR19980 |
| UL  | E29179  |

**General**

|                       |   |
|-----------------------|---|
| Product Family        | PCB Headers                               |
| Series                | <a href="#">105310</a>                    |
| Application           | Power, Wire-to-Board                      |
| Overview              | <a href="#">Nano-Fit Power Connectors</a> |
| Packaging Alternative | <a href="#">1053104610</a>                |
| Product Name          | Nano-Fit                                  |
| UPC                   | 887191937304                              |

**Physical**

|                                |                        |
|--------------------------------|------------------------|
| Breakaway                      | No                     |
| Circuits (Loaded)              | 10                     |
| Circuits (maximum)             | 10                     |
| Color - Resin                  | Natural                |
| Durability (mating cycles max) | 50                     |
| Flammability                   | 94V-0                  |
| Glow-Wire Capable              | Yes                    |
| Guide to Mating Part           | No                     |
| Keying to Mating Part          | Yes                    |
| Lock to Mating Part            | Yes                    |
| Material - Metal               | Brass                  |
| Material - Plating Mating      | Gold                   |
| Material - Plating Termination | Tin                    |
| Material - Resin               | Liquid Crystal Polymer |
| Net Weight                     | 0.910/g                |
| Number of Rows                 | 2                      |
| Orientation                    | Vertical               |
| PC Tail Length                 | 3.20mm                 |
| PCB Locator                    | Yes                    |
| PCB Retention                  | Yes                    |
| PCB Thickness - Recommended    | 1.60mm, 2.40mm         |
| Packaging Type                 | Tray                   |
| Pitch - Mating Interface       | 2.50mm                 |
| Pitch - Termination Interface  | 2.50mm                 |
| Plating min - Mating           | 0.762µm                |
| Plating min - Termination      | 1.524µm                |
| Polarized to Mating Part       | Yes                    |
| Polarized to PCB               | Yes                    |



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[105310 Series](#)

**Mates With**

Nano-Fit Receptacle Housing [1053082210](#)

|                                    |   |
|------------------------------------|---|
| Shrouded                           | Yes   |
| Stackable                          | No  |
| Surface Mount Compatible (SMC)     | No  |
| Temperature Range - Operating      | -40° to +115°C  |
| Termination Interface: Style       | Through Hole  |
| <b>Electrical</b>                  |   |
| Current - Maximum per Contact      | 7.5A  |
| Voltage - Maximum                  | 250V AC (RMS)/DC  |
| <b>Material Info</b>               |   |
| <b>Reference - Drawing Numbers</b> |   |
| Application Specification          | AS-105300-100-001   |
| Packaging Specification            | PK-105309-100-000   |
| Product Specification              | 1053001000-PS-CH-000, 1053001000-PS-ES-000,<br>1053001000-PS-JP-000, 1053001000-PS-SK-000,<br>PS-105300-100-001 |
| Sales Drawing                      | SD-105310-100-000   |
| Symbol/Footprint Data              | SYM-105310-XX10-001   |
| Test Summary                       | 1053000000-TS-000   |

This document was generated on 10/04/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[105310-2310](#)