

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1062841025](#)
Status: **Active**
Overview: Optical Connectivity Solutions
Description: CXP Optical Cable Assembly (iPass+), MTP-to-MTP, Multimode, 50/125µm, Round Cable Assembly, Straight Boot, High Bandwidth, OFNP, Cable Diameter 5.40mm, Cable Length 25.00m

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Fiber Optic Assemblies
Series	106284
Boot Type	Straight
Connector to Connector	MTP-to-MTP
Mode	Multimode
Overview	Optical Connectivity Solutions
Product Name	CXP, iPass+, MTP
UPC	883906550219

Physical

Cable Length	25.0m
Cable Size	3.80mm
Fiber (Core/Cladding)	50/125µm
Net Weight	411.500/g
Single Ended	No
Wire/Cable Type	Fiber Optic, Round

Material Info

Reference - Drawing Numbers

Sales Drawing	SD-106284-0001-001
---------------	--------------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[106284 Series](#)

Mates With

CXP Optical Transceivers

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[106284-1025](#)