

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200020475](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change (M12) Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), 20 AWG, 3.0m (9.84') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120002</a>
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67, IP68
Material - Contact	Copper Alloy
Overview	<a href="#">Brad Micro-Change (M12) Connectors</a>
Product Name	Micro-Change (M12)
Type	Double Ended
UPC	883906488062

**Physical**

Cable Diameter	6.10mm (.240")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Gray
Coupling Style	Threaded
Gender	Female-Male
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	PVC
Material - Coupling Nut	Teflon Nickel-plated Brass
Material - O-Ring	Viton
Material - Plating Mating	Gold
Net Weight	90.010/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	0° to +75°C
Wire Size AWG	20
Wire/Cable Type	Unshielded PVC

**Electrical**


Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

**Material Info**

Engineering Number	884030J11M010
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120002-005-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2021)4569-DC (8  
July 2021)

Lead

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

ZZCERT\_CE -

Declaration of

Conformity

**China RoHS**

50 Image

Not Relevant

Not Contained

CER\_4000380967\_00\_000.pdf

**Search Parts in this Series**

[120002](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200020475](#)