

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1200270090](#)
Status: **Active**
Overview:
Description: Nano-Change (M8) Single-Ended Cordset, 3 Poles, Female (90°) to Pigtail, 0.25mm² PVC Cable, 2.0m (6.56') Length

Agency Certification

UL E152210

General

Product Family Industrial Cordsets
 Series [120027](#)
 Connector End A Nano-Change (M8)
 Connector End B Pigtail
 IP Rating IP67
 Material - Contact Copper Alloy
 Overview [nanochange_40m841_products](#)
 Product Name Nano-Change (M8)
 Protocol N/A
 Region Europe
 Type Single Ended
 UPC 883906026318

Physical

Cable Diameter 4.70mm (.185")
 Cable Length 2.0m (6.56')
 Color - Cable Jacket Black
 Coupling Style Threaded
 Gender Female-Pigtail
 Keyway A-coded
 LED Indicator No
 Material - Cable Jacket PVC
 Material - Connector Body PUR
 Material - Coupling Nut Nickel-plated Brass
 Material - O-Ring Fluoro-elastomer
 Material - Plating Mating Gold
 Net Weight 78.817/g
 Orientation 90° to Pigtail
 Poles 3
 Temperature Range - Operating -25°C to +80°C
 Wire Size AWG 24
 Wire/Cable Type UL 2464

Electrical

Current - Maximum per Contact 3.0A
 Voltage - Maximum 60V AC / 75V DC

Material Info

Engineering Number 403001E02M020

Reference - Drawing Numbers

Sales Drawing 1200868179-000

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[120027](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120027-0090](#)