

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200688096](#)  
**Status:** **Active**  
**Overview:**  
**Description:** Micro-Change (M12) In-Line Splitter, 4 Pole, 1 x 4-Pole Male (Straight) to 2 x 3-Pole Female (Straight), 18 AWG TPE Cable, 4.0m Length

**Agency Certification**

UL E152210

**General**

Product Family Industrial Tees and Splitters  
 Series [120068](#)  
 IP Rating IP67  
 Overview microchange\_m12\_connectors  
 Product Name Micro-Change (M12)  
 Type Splitter - In-line  
 UPC 883906416010

**Physical**

Color - Cable Jacket Black  
 Drop Connector Micro-Change (M12)  
 Drop Gender Male  
 Keyway Single  
 LED Indicator No  
 Left Trunk Connector Micro-Change (M12)  
 Left Trunk Gender Female  
 Leg 1 Length 0.30m  
 Leg 2 Length 0.30m  
 Material - Cable Jacket PVC  
 Material - Connector Body PUR  
 Material - Coupling Nut Nickel-plated Brass  
 Net Weight 49.945/g  
 Poles 3 Female/4 Male  
 Right Trunk Connector Micro-Change (M12)  
 Right Trunk Gender Female  
 Temperature Range - Operating -30°C TO +80°C

**Electrical**

Current - Maximum per Contact 4.0A  
 Voltage - Maximum 250V AC/DC

**Material Info**

Engineering Number 884A30E03M003

**Reference - Drawing Numbers**

Sales Drawing SD-120068-029

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[120068](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200688096](#)