

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200708180

Status:

Active

Overview:

Brad Micro-Change (M12) Connectors

Description:

Micro-Change (M12) 3 Poles, Front Panel Mount Receptacle, 1/4" - 14 NPT Threads, 22 AWG PVC Leads, 0.305m (1.0') Length

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	LR6837
UL	E152210
General	
Product Family	Industrial Receptacles
Series	120070
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	Brad Micro-Change (M12) Connectors
Product Name	Micro-Change (M12)
Type	Single Ended (pigtail)
UPC	78172540956
Physical	
Coupling Type	External Thread
Gender	Female
Keyway	Single
Length	0.305m
Material - Component	Nickel-plated Zinc Die-Cast
Mounting Thread Size	1/2" - 14 NPT
Net Weight	102.000/g
Orientation	Straight
Panel Mount	Front
Poles	5
Temperature Range - Operating	-20° to +80°C
Wire Size AWG	22
Wire/Cable Type	UL 1061
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC
Material Info	
Engineering Number	8R5A06A18A120
Reference - Drawing Numbers	
Sales Drawing	SD-120070-051-001

EU ELV

Not Reviewed

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

Lead

Halogen-Free Status

Not Relevant

For more information, please visit

Contact US

China ROHS

Not Relevant

ELV

Not Reviewed

RoHS Phthalates

Not Contained

Search Parts in this Series

120070 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120070-8180](#)