



**SPECIFICATIONS:**

**MICRO-CHANGE FEMALE:**

- COUPLING NUT MATERIAL: NICKEL PLATED BRASS
- CONTACT MATERIAL: GOLD/NICKEL OVER COPPER ALLOY
- INSERT MATERIAL: BLACK PUR
- OVERMOLD: BLACK PUR
- SEALING: O-RING, VITON
- CONNECTOR HEAD UNSHIELDED - DRAIN WIRE TO PIN 5

CABLE: #22/4 w/ BRAIDED SHIELD AND #22 DRAIN WIRE  
 OUTER JACKET: BLACK, PVC  
 INNER JACKET: PVC

RATINGS: 250V, 4A  
 ENVIRONMENTAL: -25°C TO +80°C, IP67

SAP P/N#	"L" (INCH)	"L" (mm)
1200795101	9.84' +0.59' / -0.0'	250mm +15 / -0.0
1200790331	17.72' +0.78' / -0.0'	450mm +20 / -0.0
1200790332	24.01' +0.78' / -0.0'	610mm +20 / -0.0

CUSTOMER PRODUCTION APPROVAL  
 APPROVED BY: \_\_\_\_\_  
 DATE: \_\_\_\_\_  
 MUST BE SIGNED AND RETURNED BEFORE  
 PRODUCTION WILL BEGIN.

REVISED LENGTHS AND TOL  
 EC NO: IFC2018-0052  
 DRWN: AAKHTAR 2017/07/19  
 CHKD: MZIELINS 2017/07/24  
 APPR: BWOODMAN 2010/03/08

QUALITY SYMBOLS  
 ▽=0  
 ▽C=0

GENERAL TOLERANCES (UNLESS SPECIFIED)		
	mm	INCH
4 PLACES	±-	±---
3 PLACES	±-	±.005
2 PLACES	±0.13	±.010
1 PLACE	±0.25	±.020
ANGULAR ±1/2°		
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		

DIMENSION STYLE -  
 DRAWN BY DATE  
 CHECKED BY DATE  
 LHARTMAN 2010/01/12  
 APPROVED BY DATE  
 JFMURPHY 2010/03/08  
 MATERIAL NO.  
 SEE CHART

SCALE NTS DESIGN UNITS INCH  
 THIRD ANGLE PROJECTION  
 TITLE MICRO-CHANGE ULOCK ASSY 5P FEM 90DEG #22/4AWG + DRAIN, PVC  
 MOLEX MOLEX INCORPORATED  
 DOCUMENT NO. SD-120079-021 SHEET NO. 1 OF 1  
 THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

RESTRICTED SALES DRAWING

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120079-5101](#)