


NOTE: DRAIN WIRE CONNECTED TO THE PIN 5 AND COUPLING NUT

MOLEX P/N	ENGINNERING No.:	L[mm]
1200980003	BB5S30PP4M002	200
1200980004	BB5S30PP4M003	300
1200980005	BB5S30PP4M006	600
1200980006	BB5S30PP4M010	1000
1200980007	BB5S30PP4M020	2000
1200980008	BB5S30PP4M030	3000
1200980009	BB5S30PP4M040	4000
1200980010	BB5S30PP4M050	5000
1200980011	BB5S30PP4M070	7000
1200980012	BB5S30PP4M080	8000
1200980013	BB5S30PP4M090	9000
1200980014	BB5S30PP4M100	10000
1200980015	BB5S30PP4M118	11800
1200980017	BB5S30PP4M200	20000
1200980018	BB5S30PP4M243	24300
1200980143	BB5S30PP4M005	500
1200980144	BB5S30PP4M009	900
1200980146	BB5S30PP4M007	700
1200980147	BB5S30PP4M120	12000
1200980148	BB5S30PP4M060	6000
1200980160	BB5S30PP4M150	15000
1200980171	BB5S30PP4M170	17000
1200980176	BB5S30PP4M190	19000
1200980178	BB5S30PP4M420	42000

LENGTH (mm):	TOLERANCE
To 3000 mm	-0/ +50 mm
From 3100 to 6000	-0/ +75 mm
More than 6000	-0/ +100 mm

### PART No MATRIX



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		CURRENT REV DESC: OBSOLETE PART NUMBER			
DIMENSION UNITS: mm		SCALE: NTS			
GENERAL TOLERANCES (UNLESS SPECIFIED)				CSE M12 M12 5P BC FE STR PUR MA STR XM DE SHLD BRA	
				PRODUCT CUSTOMER DRAWING	
4 PLACES ±		3 PLACES ±		DOCUMENT NUMBER: SD-120098-040	
3 PLACES ±		2 PLACES ±		DOC TYPE: PSD	
2 PLACES ±		1 PLACE ±		DOC PART: 001	
1 PLACE ±		0 PLACES ±		REVISION: A2	
ANGULAR TOL ± °		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		SHEET NUMBER: 1 OF 1	
THIRD ANGLE PROJECTION		DRAWING: A3-SIZE		SERIES: 120098	
MATERIAL NUMBER: SEE CHART		CUSTOMER: GENERAL MARKET			

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200980143](#)