

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1200988025](#)  
**Status:** **Active**  
**Overview:** PROFIBUS Solutions  
**Description:** PROFIBUS Straight D-Sub Connector to Pigtail, 22 AWG, PUR Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120098</a>
Connector End A	D-Sub (9-pin)
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	N/A
Overview	<a href="#">PROFIBUS Solutions</a>
Product Name	PROFIBUS
Protocol	N/A
Region	America, Asia, Europe
Type	Single Ended
UPC	883906560096

**Physical**

Cable Diameter	N/A
Cable Length	1.0m (3.28')
Color - Cable Jacket	Purple
Coupling Style	Threaded
Gender	Male-Pigtail
Keyway	None
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	N/A
Material - Coupling Nut	Gray Anodized Aluminum
Material - Plating Mating	N/A
Orientation	90° to Pigtail
Poles	9
Temperature Range - Operating	0° to +60°C
Wire Size AWG	22
Wire/Cable Type	Shielded-Twisted Pair

**Electrical**

Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

**Material Info**

Engineering Number	M03S07PP4M010
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120098-041-001
---------------	-------------------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120098](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1200988025](#)