

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1201080021](#)
Status: **Active**
Overview: Brad Industrial Ethernet Solutions
Description: Micro-Change (M12) Double-Ended Cordset, 4 Poles, Male (90°) to Male (90°), 26 AWG, PVC Cable, 23.0m (9.84') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120108
Connector End A	Micro-Change (M12)
Connector End B	Micro-Change (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad Industrial Ethernet Solutions
Performance Category	5e
Product Name	Micro-Change (M12)
Region	America, Asia, Europe
Type	Double Ended
UPC	78678889818

Physical

Cable Diameter	6.35mm (.250")
Cable Length	23.0m (75.46')
Color - Cable Jacket	Blue Green
Coupling Style	Threaded
Gender	Male-Male
Keyway	D-coded
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPU
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Net Weight	1029.653/g
Orientation	90° to 90°
Poles	4
Temperature Range - Operating	-25° to +75°C
Wire Size AWG	26
Wire/Cable Type	Shielded-Stranded

Electrical


Current - Maximum per Contact	1.5A
Voltage - Maximum	125V

Material Info

Engineering Number	E11A06302M230
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-120108-036-001
---------------	-------------------



EU ELV

Compliant with Exemption 3

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2021)4569-DC (8 July 2021)

Lead

Halogen-Free

Status

Not Relevant

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Not Relevant

Compliant with

Exemption 3

Not Contained

Search Parts in this Series

[120108 Series](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1201080021](#)