



FRONT VIEW - MALE M12




- 1-WHITE/ORANGE
- 2-WHITE/GREEN
- 3-ORANGE
- 4-GREEN

FRONT VIEW - MALE M12



- 1-WHITE/ORANGE
- 2-WHITE/GREEN
- 3-ORANGE
- 4-GREEN



NOTES:

MECHANICAL

M12 CONNECTOR

- INSERT: BLACK PUR
- CONTACT: GOLD/NICKEL OVER COPPER ALLOY
- COUPLING NUT: NICKEL PLATED BRASS
- MOLDED BODY: BLACK PUR

- CABLE: 24 AWG 2 PAIR CONDUCTORS BLUE TPE JACKET
- UL LISTED: CMR
- CSA LISTED: CMG

WRAP LABEL: MARKED WITH P/N, DATE CODE, VOLTAGE & AMPERAGE

ELECTRICAL

- ACCORDING TO CAT5e
- VOLTAGE RATING: 30V AC/DC
- AMPERAGE: 1.5A

ADDED PART NO. TABLE EC NO: IPG2015-2010 DRWN: GGUSTAFS 2015/05/22 CHKD: BARDEN 2015/07/16 APPR: BWOODMAN 2013/04/18	DESCRIPTION REV	QUALITY SYMBOLS ▽=0 ▽C=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE INCH ONLY		SCALE NTS	DESIGN UNITS INCH	THIRD ANGLE PROJECTION		
			mm	INCH	DRAWN BY	DATE	TITLE MICRO-CHANGE 4P MALE/MALE M12 ST/ST #24-2P BLUE TPE CAT5E				
		4 PLACES	±---	±---	BARDEN	2013/01/29					
		3 PLACES	±---	±.005	CHECKED BY	DATE	MOLEX INCORPORATED				
2 PLACES	±0.13	±.010	TWOLEGE	2013/03/01							
1 PLACE	±0.25	±.020	APPROVED BY	DATE	MATERIAL NO. SEE MATRIX		DOCUMENT NO. SD-120108-052		SHEET NO. 1 OF 2		
ANGULAR ±.5°			JFMURPHY	2013/04/18							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE B		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Molex:

[1201080527](#) [1201080533](#)