

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1201150050](#)  
**Status:** **Active**  
**Overview:** Brad Micro-Change (M12) Connectors  
**Description:** Micro-Change Molded Junction Box, Side Mount, Single Keyway with Mini-Change B-Size Molded Home Run Connector, 6 Ports, PNP, 0.30m Cable Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Passive Distribution Boxes
Series	<a href="#">120115</a>
IP Rating	IP67
NEMA Rating	NEMA 6
Overview	<a href="#">Brad Micro-Change (M12) Connectors</a>
Product Name	Micro-Change (M12)
UPC	78678824064

**Physical**

Bus I/O	Micro-Change (M12)
Cable Connector Orientation	Straight
Cable Length	N/A
Home Run Cable Length	0.305m
Home Run Connector	Micro-Change (M12) - 8 pole
Home Run Interface	Integrated Connector
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Housing	PBT
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Orientation	Side Mount
Poles	5
Poles (wired)	4
Ports	6
Temperature Range - Operating	-20°C to +90°C
Wiring Configuration	Single I/O per Port

**Electrical**


Current - Maximum per Contact	4.0A per port
Functional Wiring	PNP
Voltage - Maximum	10-30V DC

**Material Info**

Engineering Number	803P602
--------------------	---------

**Reference - Drawing Numbers**

Sales Drawing	SD-120115-008
---------------	---------------



**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120115 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1201150050](#)