

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202010048](#)

**Status:** **Active**

**Overview:**

**Description:** Ultra-Lock (M12) Single-Ended Cordset, 8 Poles, Male (Straight) to Pigtail, 24 AWG, PUR Cable, 4.0m (13.12') Length, Yellow

**General**

Product Family	Industrial Cordsets
Series	<a href="#">120201</a>
Connector End A	Ultra-Lock (M12)
Connector End B	Pigtail
IP Rating	IP68
Material - Contact	Copper Alloy
Overview	ultralock_connection_system
Product Name	Ultra-Lock (M12)
Protocol	N/A
Region	America
Type	Single Ended
UPC	78678809506

**Physical**

Cable Diameter	6.60mm (.260")
Cable Length	4.0m (13.12')
Color - Cable Jacket	Yellow
Coupling Style	Push to Lock
Gender	Male-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR
Material - Connector Body	PUR
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold
Orientation	Straight to Pigtail
Poles	8
Temperature Range - Operating	-25° to +90°C
Wire Size AWG	24
Wire/Cable Type	EU Cable

**Electrical**

Current - Maximum per Contact	2.0A
Voltage - Maximum	30V

**Material Info**

Engineering Number	W08S06P19M040
--------------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120083-022-001
---------------	-------------------

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120201](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1202010048](#)