

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1202300129](#)

Status: **Active**

Overview:

Description: Brad M23 Signal Connector, Straight Male, Crimp Contacts, 9 (8+1) Poles, Cable Diameter 11.00-17.00mm

General

| | |
|--------------------|---|
| Product Family | Field Attachable / Accessories |
| Series | 120230 |
| Application | Signal |
| Comments | Crimp Range 0.14-1.00mm ² / 0.75-2.50mm ² |
| IP Rating | IP67 |
| Material - Contact | Brass |
| Overview | m23_connectivity |
| Product Name | Brad M23 |
| Type | Field Attachable Connector |
| UPC | 883906299361 |

Physical

| | |
|-------------------------------|----------------------------|
| Cable Diameter | 11.00-17.00mm (.433-.669") |
| Coupling Type | N/A |
| Diagnostics / LEDs | No |
| Diagnostics Port | No |
| Gender | Male |
| Keyway | None |
| Material - Connector Body | Nylon |
| Material - Coupling Nut | N/A |
| Material - Plating Mating | Gold |
| Orientation | Straight |
| Poles | 9 (8+1) |
| Temperature Range - Operating | -40°C to +125°C |
| Wire Size AWG | N/A |

Electrical

| | |
|-------------------------------|-------------|
| Current - Maximum per Contact | 20.0A, 8.0A |
| Voltage - Maximum | 300V |

Material Info

| | |
|--------------------|-------------|
| Engineering Number | KAS9S06-419 |
|--------------------|-------------|

EU ELV

Not Reviewed

EU RoHS

Not Reviewed

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

Search Parts in this Series

[120230](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1202300129](#)