

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202310053](#)  
**Status:** **Active**  
**Overview:** Brad M23 Signal and Power Connectors  
**Description:** Brad M23 Signal Connector, Front Panel-Mount Receptacle, 90° Male Flange Mount 4xØ 2.70mm, Rotatable, Crimp Contacts, 12 Poles

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Field Attachable / Accessories
Series	<a href="#">120231</a>
Application	Signal
Comments	Crimp Range 0.14-1.00mm <sup>2</sup>
IP Rating	IP67
Material - Contact	Brass
Overview	<a href="#">Brad M23 Signal and Power Connectors</a>
Product Name	Brad M23
Type	Field Attachable Connector
UPC	883906300289

**Physical**

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Male
Keyway	None
Material - Connector Body	Nylon
Material - Coupling Nut	N/A
Material - Plating Mating	Gold
Orientation	90° Angle
Poles	12
Temperature Range - Operating	-40°C to +125°C
Wire Size AWG	N/A

**Electrical**

Current - Maximum per Contact	8.0A
Voltage - Maximum	300V

**Material Info**

Engineering Number	KRSCG27-0112
--------------------	--------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120231-003-001
---------------	-------------------



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[120231 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1202310053](#)