

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1202320064](#)  
**Status:** **Active**  
**Overview:** Brad M23 Signal and Power Connectors  
**Description:** Brad M23 Signal Connector, Male Contact Ø 1.5mm, Crimp Range 0.14-1.00mm2

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                    |                                                      |
|--------------------|------------------------------------------------------|
| Product Family     | Field Attachable / Accessories                       |
| Series             | <a href="#">120232</a>                               |
| Comments           | Male Contact 1.5mm                                   |
| IP Rating          | IP67                                                 |
| Material - Contact | Brass                                                |
| Overview           | <a href="#">Brad M23 Signal and Power Connectors</a> |
| Product Name       | Brad M23                                             |
| Type               | Field Attachable Connector                           |
| UPC                | 883906301293                                         |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Diameter                | N/A             |
| Coupling Type                 | N/A             |
| Diagnostics / LEDs            | No              |
| Diagnostics Port              | No              |
| Gender                        | Male            |
| Keyway                        | None            |
| Material - Connector Body     | N/A             |
| Material - Coupling Nut       | N/A             |
| Material - Plating Mating     | Gold            |
| Net Weight                    | 0.260/g         |
| Orientation                   | Straight        |
| Poles                         | N/A             |
| Temperature Range - Operating | -40°C to +125°C |
| Wire Size AWG                 | N/A             |

**Electrical**

|                               |     |
|-------------------------------|-----|
| Current - Maximum per Contact | N/A |
| Voltage - Maximum             | N/A |

**Material Info**

|                    |          |
|--------------------|----------|
| Engineering Number | KCS06-10 |
|--------------------|----------|

**Reference - Drawing Numbers**

|               |                   |
|---------------|-------------------|
| Sales Drawing | SD-120232-064-001 |
|---------------|-------------------|

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Contained Per -ED/01/2018 (15 January 2018)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

50 Image

Not Reviewed

Not Contained

**Search Parts in this Series**

[120232 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1202320064](#)