

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1205010001](#)
Status: **Active**
Overview: Brad M12 Power Connector System
Description: Brad M12 Power Double-Ended Cordset, 4 Poles, Female (Straight) to Male (Straight), F-Coded, 14 AWG, TC-ER (K18) Cable, 1.0m (3.78') Length

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-120500-001-001 \(PDF\)](#)

General

Product Family	Industrial Cordsets
Series	120501
Application	Power
Connector End A	Ultra-Lock (M12)
Connector End B	Ultra-Lock (M12)
IP Rating	IP67
Material - Contact	Copper Alloy
Overview	Brad M12 Power Connector System
Product Name	Brad M12 Power
Protocol	N/A
Type	Double Ended
UPC	78172540694

Physical

Cable Diameter	17.53-22.35mm (.690-.880")
Cable Length	1.0m (3.28')
Color - Cable Jacket	Black
Coupling Style	Push to Lock
Gender	Female-Male
Keyway	F-coded
Material - Cable Jacket	TPE
Material - Connector Body	Nickel-plated Brass
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Fluoro-elastomer
Material - Plating Mating	Gold over Nickel
Net Weight	201.848/g
Orientation	Straight to Straight
Poles	4
Temperature Range - Operating	-20°C to +90°C
Wire Size AWG	14
Wire/Cable Type	TC-ER

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	300V AC/DC

Material Info

Engineering Number	FFP4030K18M010
--------------------	----------------

Reference - Drawing Numbers

Product Specification	PS-120500-001-001
Sales Drawing	SD-120501-001

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/108/2014 (17 Dec 2014)

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS	50 Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[120501](#) Series

Mates With

Brad M12 F-Coded Power Receptacles
[120502](#)

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[120501-0001](#)