

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1212080230](#)  
**Status:** **Active**  
**Overview:** mPm DIN Valve Connectors  
**Description:** mPm DIN Valve Connector, Form B-11mm, External Thread, 2 Pole Plus Ground with C4 Circuit, 24V, Red LED, Nitrile Gasket, Bulk Pack, Mounted

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Packaging Specification PK-121208-S22-001 \(PDF\)](#)

**General**

|                    |  |
|--------------------|--|
| Product Family     | Field Attachable / Accessories           |
| Series             | <a href="#">121208</a>                   |
| Form               | B - 11mm                                 |
| IP Rating          | IP65, IP67                               |
| Material - Contact | Brass                                    |
| Overview           | <a href="#">mPm DIN Valve Connectors</a> |
| Product Name       | mPm                                      |
| Type               | Field Attachable Connector               |
| UPC                | 884982511484                             |

**Physical**

|                               |                 |
|-------------------------------|-----------------|
| Cable Diameter                | N/A             |
| Coupling Type                 | External Thread |
| Diagnostics / LEDs            | Yes             |
| Diagnostics Port              | No              |
| Gender                        | N/A             |
| Keyway                        | None            |
| Material - Connector Body     | Polyamide       |
| Material - Coupling Nut       | N/A             |
| Material - Plating Mating     | Silver          |
| Net Weight                    | 19.814/g        |
| Orientation                   | 90° Angle       |
| Pitch - Mating Interface      | 11.00mm         |
| Poles                         | 2               |
| Temperature Range - Operating | -40°C to +90°C  |
| Wire Size AWG                 | 16              |

**Electrical**

|                               |       |
|-------------------------------|-------|
| Current - Maximum per Contact | 16.0A |
| Voltage - Maximum             | 24V   |

**Material Info**

|                    |                |
|--------------------|----------------|
| Engineering Number | S22200TC422RSN |
|--------------------|----------------|

**Reference - Drawing Numbers**

|                         |                   |
|-------------------------|-------------------|
| Packaging Specification | PK-121208-S22-001 |
| Sales Drawing           | SD-121208-001-001 |



*Series image - Reference only*

**EU ELV**

**Compliant with Exemption 3**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

**China RoHS**

ELV

Not Relevant

Compliant with

Exemption 3

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[121208](#) Series

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1212080230](#)