

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1300080165](#)
Status: **Active**
Overview:
Description: Mini-Change C-Size Single-Ended Cordset, 12 Poles, Female (Straight) to Pigtail, 16 AWG, PVC Cable, 6.10m (20.0') Length

Agency Certification

CSA	LR6837
UL	E152210

General

Product Family	Industrial Cordsets
Series	130008
Connector End A	Mini-Change
Connector End B	Pigtail
IP Rating	IP67
Material - Contact	Brass
Overview	minichange_products
Product Name	Mini-Change
Protocol	DeviceNet
Region	America
Type	Single Ended
UPC	78678840760

Physical

Cable Diameter	18.03mm (.710")
Cable Length	6.10m (20.0')
Color - Cable Jacket	Yellow
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PVC
Material - Connector Body	TPE
Material - Coupling Nut	Black Epoxy Coated Zinc
Material - Plating Mating	Gold
Net Weight	744.000/g
Orientation	Straight to Pigtail
Poles	12
Temperature Range - Operating	-20°C to +105°C
Wire Size AWG	16
Wire/Cable Type	STOOW

Electrical

Current - Maximum per Contact	5.0A
Voltage - Maximum	600V

Material Info

Engineering Number	302000A01F200
--------------------	---------------

Reference - Drawing Numbers

Sales Drawing	SD-130008-014-001
---------------	-------------------

EU ELV

Not Relevant

EU RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Reviewed

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

[130008](#) Series

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300080165](#)