

10

9

8

7

6

5


4

3

2

1


FACE VIEW-FEMALE INSERT



- 1 VIOLET
- 2 RED
- 3 GRAY
- 4 RED/BLUE
- 5 BLUE
- 6 GREEN
- 7 BROWN
- 8 WHITE/GREEN
- 9 WHITE/YELLOW
- 10 WHITE/GREY
- 11 BLACK
- 12 GREEN/YELLOW
- 13 YELLOW/BROWN
- 14 BROWN/GREEN
- 15 WHITE
- 16 YELLOW
- 17 PINK
- 18 GREY/BROWN
- 19 GREY/PINK

CUSTOMER PRODUCTION APPROVAL
 APPROVED BY: _____
 DATE: _____
 MUST BE SIGNED AND RETURNED BEFORE
 PRODUCTION WILL BEGIN.

RESTRICTED SALES DRAWING



MATERIALS:

- MOLDED BODY: YELLOW PVC
- COUPLERS: STAINLESS STEEL
- CONTACTS: GOLD/NICKEL OVER COPPER ALLOY
- INSERTS: YELLOW PVC
- CABLE: BLACK PUR
- CABLE JACKET: 3-#18 AWG AND 16-#22 AWG
- GAUGE: PVC (SEE PINOUT FOR COLORS)
- CONDUCTOR INSULATION: -25° TO 90°C
- TEMPERATURE RANGE:
- ELECTRICAL:
- CURRENT RATING: 3 AMP - 18 AWG
- 2 AMP - 22 AWG
- VOLTAGE RATING: 300V
- MECHANICAL:
- INGRESS PROTECTION: IP 67

PART NUMBER	ENGINEERING NO.	FINISH LENGTH
TBD	303000B20M0601	19.69FT. +6.50IN -0IN [6M +16.51CM -0CM]

EC NO: WEU2010-0167 DRWN: TWOLDEGE 11/4/09 CHKD: LHARTMAN APPR: JFMURPHY 2010/01/04	DESCRIPTION REV	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ±---- ±---- 3 PLACES ±---- ±---- 2 PLACES ±---- ±---- 1 PLACE ±---- ±---- ANGULAR ±----° DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	DIMENSION STYLE	SCALE	DESIGN UNITS	THIRD ANGLE PROJECTION MINI CHANGE CORESET 19-POLE FEMALE STRAIGHT BLACK PUR CABLE MOLEX INCORPORATED SD-130008-021 SHEET NO. 1 OF 1
		▽=0		----	INCH	INCH	
		∇=0		----	DATE	DATE	
		∇=0		----	DATE	DATE	
A	REV			SEE CHART			

10

9

8

7

6

5

4

3

2

1

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300080497](#)