

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1300250267](#)  
**Status:** **Active**  
**Overview:** [Brad Mini-Change Connectors](#)  
**Description:** Mini-Change Single-Ended Cordset, 5 Poles, Male (90°) to Female (90°), 16 and 20 AWG, DeviceNet Mid Cable, 1.0m (3.28') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR6837

**General**

Product Family Industrial Cordsets  
 Series [130025](#)  
 Connector End A Mini-Change  
 Connector End B Mini-Change  
 IP Rating IP67  
 Material - Contact Brass  
 Overview [Brad Mini-Change Connectors](#)  
 Product Name DeviceNet Trunk, Mini-Change  
 Region Europe  
 Type Double Ended  
 UPC 78678888470

**Physical**

Cable Diameter 8.38mm (.330")  
 Cable Length 1.0m (3.28')  
 Color - Cable Jacket Gray  
 Coupling Style Threaded  
 Gender Female-Male  
 Keyway Single  
 LED Indicator No  
 Material - Cable Jacket PVC  
 Material - Connector Body PVC  
 Material - Coupling Nut Die-Cast Zinc  
 Material - Plating Mating Gold  
 Orientation 90° to 90°  
 Poles 5  
 Temperature Range - Operating -20° to +80°C  
 Wire Size AWG 16, 20  
 Wire/Cable Type Mid Cable

**Electrical**


Current - Maximum per Contact 4.0A  
 Voltage - Maximum 300V AC/DC

**Material Info**

Engineering Number DNB99A-M010

**Reference - Drawing Numbers**

Sales Drawing SD-130025-011-001



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

For more information, please visit [Contact US](#)

China ROHS

Not Reviewed

ELV

Not Reviewed

RoHS Phthalates

Not Reviewed

**Search Parts in this Series**

[130025 Series](#)

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300250267](#)