



MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130028-0022	DND22A-M003	.98' +.75" -0 [.3M +19.1 -0]
130028-0023	DND22A-M005	1.64' +1.75" -0 [.5M +44.5 -0]
130028-0027	DND22A-M009	2.95' +1.75" -0 [.9M +44.5 -0]
130028-0028	DND22A-M010	3.28' +2.19" -0 [1.0M +55.6 -0]
130028-0033	DND22A-M020	6.56' +3.50" -0 [2.0M +88.9 -0]
130028-0037	DND22A-M030	9.84' +3.50" -0 [3.0M +88.9 -0]
130028-0038	DND22A-M031	10.17' +3.50" -0 [3.1M +88.9 -0]
130028-0040	DND22A-M040	13.12' +6.50" -0 [4.0M +165.1 -0]
130028-0042	DND22A-M050	16.40' +6.50" -0 [5.0M +165.1 -0]
130028-0043	DND22A-M060	19.69' +6.50" -0 [6.0M +165.1 -0]

MATERIAL NUMBER	OLD PART NUMBER	FINISHED LENGTH
130028-0239	DND22A-M070	22.97' +6.50" -0 [7.0M +165.1 -0]
130028-0044	DND22A-M080	26.25' +12.50" -0 [8.0M +317.5 -0]
130028-0045	DND22A-M090	29.53' +12.50" -0 [9.0M +317.5 -0]
130028-0046	DND22A-M100	32.81' +12.50" -0 [10.0M +317.5 -0]
130028-0048	DND22A-M150	49.21' +24.50" -0 [15.0M +622.3 -0]
130028-0050	DND22A-M200	65.62' +24.50" -0 [20.0M +622.3 -0]
130028-0052	DND22A-M250	82.02' +24.50" -0 [25.0M +622.3 -0]
130028-0054	DND22A-M300	98.43' +24.50" -0 [30.0M +622.3 -0]



- NOTES: (D)
- MATERIAL: AS NOTED
 - FINISH: AS NOTED
 - ELECTRICAL:
VOLTAGE RATING PER IEC 60664: 300V
VOLTAGE RATING PER UL: 300V
CURRENT: 4A
 - TEMP RATING: -20° TO +80°C
 - PROTECTION: IP67 (WHEN MATED)
 - COUPLING THREAD: M12X1.0- AS NOTED.
 - AGENCY:
UL LISTED, FILE: E152210
CSA CERTIFICATION FILE: LR6837
 - ALL DIMS ARE FOR REFERENCE UNLESS NOTED OTHERWISE

PART NUMBER LEGEND

DND22A-M005

FINISHED LENGTH:
M005= 0.5 METER
M010= 1 METER
M100= 10 METER

SCHEMATIC

- | | | |
|---|---|-----------|
| 1 | → | 1 - DRAIN |
| 2 | → | 2 - V+ |
| 3 | → | 3 - V- |
| 4 | → | 4 - CAN_H |
| 5 | → | 5 - CAN_L |

ITEM	COMPONENT	MATERIAL	FINISH
1	INSERT	NYLON 6/6	BLACK
2	CONTACT SOCKET	COPPER ALLOY	GOLD OVER NICKEL
3	CONTACT PIN	COPPER ALLOY	GOLD OVER NICKEL
4	COUPLING NUT	ZINC DIE CAST	BLACK E-COATED
5	OVERMOLD	PVC	GRAY
6	CABLE-DEVICENET THIN CABLE 2/22 & 2/22 SHIELD PAIR	PVC	GRAY
7	LABEL	VINYL	BLACK/YELLOW

UPDATE NOTES EC NO.: IPG2018-0109 DRWN: AAKHTAR 2017/08/10 CHKD: RSTONE 2017/08/10 APPR: BWOODMAN	DESCRIPTION ---	QUALITY SYMBOL	GENERAL TOLERANCES (UNLESS SPECIFIED)	DIMENSION STYLE INCH/MM	SCALE ---	DESIGN UNITS INCH	THIRD ANGLE PROJECTION	
		▽=0	4 PLACES ±---	mm INCH	DRAWN BY RSTONE	DATE 2016/09/16	TITLE	MICRO-CHANGE 5P M/MFE DEVICENET CORDSET
		∇=0	3 PLACES ±---	±---	CHECKED BY M ZIELIN	DATE 2016/09/26	MOLEX INCORPORATED	
			2 PLACES ±---	±0.01	APPROVED BY	DATE	MATERIAL NO. -	DOCUMENT NO. SD-130028-001
			1 PLACE ±.3 ±---	ANGULAR ±2°		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION		
			DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300280027](#)