



POLES	MATERIAL NO.	ENG. NO.	LENGTH
3	1300630003	C03000A48M020	2M +89-0MM (6'7"+3.50-0)
4	1300630089	C04000A48M020	2M +89-0MM (6'7"+3.50-0)

FACE VIEW-FEMALE INSERT



SPECS:  
 OVERMOLD: GRAY PVC  
 INSERT: BLACK PVC  
 COUPLING NUT: ANODIZED ALUMINUM  
 CABLE: #10AWG GRAY PVC  
 DUAL RATED UL TC/OPEN WIRING & STOOO  
 ELECTRICAL: 600V AC/DC 32 AMPS

<b>UPDATED DRAWING</b> EC NO: IPG2014-1095 DRAWINGGUSTAFSON 2015/09/01 CHKD:VOU 2015/11/12 APPR: JFMURPHY 2015/09/16	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE <b>IN/MM</b>		SCALE <b>1:1</b>	DESIGN UNITS <b>INCH</b>	THIRD ANGLE PROJECTION	
		4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ±1/2°	mm INCH ± --- ± --- ± --- ± --- ± --- ± --- ± --- ± ---	DRAWN BY B. RUPERT	DATE 01/12/10	TITLE <b>QUICK CHANGE FEMALE STRAIGHT 3 &amp; 4 POLE AS PORTABLES</b>		<b>MOLEX INCORPORATED</b>	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SEE CHART	APPROVED BY JFMURPHY	DATE 2010/01/15	DOCUMENT NO. <b>SD-130063-089</b>		SHEET NO. <b>1 OF 1</b>			
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[1300630112](#)